Select 70C-10

Carbon Steel / Gas Shielded / Metal Cored

FEATURES

- Designed for single pass welding of high-speed welding of thin gauge carbon steels.
- Travel speeds of 85-100 ipm are readily achievable.
- Performance of this product is not dependent on high technology power sources; a standard CV machine produces excellent results.
- Applications include welding automotive and truck frames, automotive cradle assemblies, farm machinery and other general purpose welding of light gauge components.

DIAMETERS (in (mm))

0.045 (1.2), 1/16 (1.6), 5/64 (2.0)

POSITIONS



SHIELDING GAS

Ar + 5-25% CO2 Flow Rate: 40 - 50 CFM

POLARITY

Direct Current Electrode Positive (DCEP)

RECOMMENDED WELDING PARAMETERS

Diameter in (mm)	Shielding Gas	Position	WFS* in/min (m/min)	Amps	Volts	CTWD* in (mm)
0.045 (1.2 mm)	75% Ar/25% CO2	Flat & Horizontal	260 (6.6)	200	25	1/2 - 5/8 (13 - 16)
		Flat & Horizontal	305 (7.7)	220	26	1/2 - 5/8 (13 - 16)
		Flat & Horizontal	360 (9.1)	240	27.5	5/8 - 3/4 (16 - 19)
		Flat & Horizontal	405 (10.3)	255	29	5/8 - 3/4 (16 - 19)
1/16 (1.6 mm)	75% Ar/25% CO2	Flat & Horizontal	200 (5.1)	250	25	5/8 - 3/4 (16 - 19)
		Flat & Horizontal	245 (6.2)	290	26	5/8 - 3/4 (16 - 19)
		Flat & Horizontal	275 (7.0)	310	27.5	3/4 - 1 (19 - 25)
		Flat & Horizontal	285 (7.2)	330	29	3/4 - 1 (19 - 25)
5/64 (2.0 mm)	75% Ar/25% CO2	Flat & Horizontal	170 (4.3)	350	25	3/4 - 1 (19 - 25)
		Flat & Horizontal	185 (4.7)	370	26	3/4 - 1 (19 - 25)
		Flat & Horizontal	210 (5.3)	400	28	1 - 1 1/4 (25 - 32)
		Flat & Horizontal	255 (6.5)	415	29	1 - 1 1/4 (25 - 32)

* WFS = Wire Feed Speed, CTWD = Contact Tip To Work Distance

Welding parameters are for 75% Ar /25% CO2, at higher levels of argon the voltage should be gradually decreased: ½-1 volt for 85% Ar/15% CO2, 1-1 ½ volts for 90% Ar/10% CO2, and 1-2 volts for 95% Ar/5% CO2.



Notice: Be sure to follow all your employers safety practices, policies and procedures when using this product. Refer to CSA W117.2 and ANSI Z49.1 Safety in Welding, Cutting and Allied Processes for further information and the manufactures SDS sheet. The results reported are based upon testing of the product under controlled laboratory conditions in accordance with American Welding Society Standards. Actual use of the product may produce different results due to varying conditions. An example of such conditions would be electrode size, plate chemistry, environment, weldment design, fabrication methods, welding procedure and service requirements. Thus the results are not guarantees for use in the field. The manufacturer disclaims any warranty of merchantability or fitness for any particular purpose with respect to its products.

PRODUCT DATA SHEET

CONFORMANCES

E70C-GSM

E70C-GSM

ASME SFA 5.18

AWS A5.18

PACKAGING (lbs (kgs))

33 (15) Spools, 60 (27.2) Coils, 500 (226.8) Round Drum, 800 (362.9) Hex Drum, 900 (408.2) Hex Drum *Some packaging options may not be available depending on diameter and product. Special package options may be available upon request.

STORAGE AND HANDLING

All products should be stored in original packaging, in dry conditions and handled with care. For more information refer to our website.



Revision: 9/16/2022

Notice: Be sure to follow all your employers safety practices, policies and procedures when using this product. Refer to CSA W117.2 and ANSI Z49.1 Safety in Welding, Cutting and Allied Processes for further information and the manufactures SDS sheet. The results reported are based upon testing of the product under controlled laboratory conditions in accordance with American Welding Society Standards. Actual use of the product may produce different results due to varying conditions. An example of such conditions would be electrode size, plate chemistry, environment, weldment design, fabrication methods, welding procedure and service requirements. Thus the results are not guarantees for use in the field. The manufacturer disclaims any warranty of merchantability or fitness for any particular purpose with respect to its products.

600 Enterprise Drive, P.O. Box 259, Fort Loramie, Ohio 45845-0259 • 800-341-5215 • www.Select-Arc.com